



## Abrasive flap disc SLTflex (CER), mounting M14, 115 mm Ø, Grit: 60



### Order data

Order number	566312 60
GTIN	4027497550586
Item class	53L

### Description

#### Version:

The **sickle-shaped strips** (patented) are radially linked to a high-strength GRP centre. The **pad-less design** permits an **extremely large overlap between strips**. Very high coating density. M14 threaded mounting, **no clamping nut required**.

**Ceramic grit (CER)** with active upper layer bonding for **heavy duty**.

#### Application:

For use in **inaccessible places**, contour grinding and for **grinding out of weld fillets**. Large overlap between strips permits **soft cutting**.

### Technical description

Grit	60
Shape description	dished with overlap between strips
Disc Ø	115 mm
Series	SLTflex
Grinding medium code	Ceramic

Iron, sulphur and chlorine constituents	<0.1 %
Product name attribute	115 mm Ø
Thread	M14
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
dry	suitable		