



Abrasive flap disc SLTflex (CER), mounting M14, 125 mm Ø, Grit: 40



Order data

Order number	566313 40
GTIN	4027497550593
Item class	53L

Description

Version:

The **sickle-shaped strips** (patented) are radially linked to a high-strength GRP centre. The **pad-less design** permits an **extremely large overlap between strips**. Very high coating density. M14 threaded mounting, **no clamping nut required**.

Ceramic grit (CER) with active upper layer bonding for **heavy duty**.

Application:

For use in **inaccessible places**, contour grinding and for **grinding out of weld fillets**. Large overlap between strips permits **soft cutting**.

Technical description

Shape description	dished with overlap between strips
Grit	40
Disc Ø	125 mm
Series	SLTflex
Grinding medium code	Ceramic

Iron, sulphur and chlorine constituents	<0.1 %
Product name attribute	125 mm Ø
Thread	M14
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
dry	suitable		