



## Segment jaws set, 3 pieces, Steel, for chuck type: 250



### Order data

Order number	313435 250
GTIN	2050001929525
Item class	33T

### Description

**Version:**

**Precision milled** slots and **precision ground** serrations, **burnished**.

**Application:**

All-round low-distortion clamping.

**Material:**

Quality product made of 16MnCr5.

**Suitable for:**

**Heavy-duty chucks** from Schunk, Röhmm and other heavy-duty chuck manufacturers.

**Optional extras:**

T-nuts No. 313505 – 313605.

**Note:**

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

for chuck type	250 mm
Height H	70 mm
Length L	80 mm
Bore spacing b	28 mm
Hole centre spacing a	30 mm
Width B	180 mm

Slot width D	21 mm
Type of product	Heavy-duty lathe chuck jaws