



## Top jaws set, 3 pieces, for chuck type: 210



### Order data

|              |               |
|--------------|---------------|
| Order number | 313715 210    |
| GTIN         | 2050001929693 |
| Item class   | 33T           |

### Description

**Version:**

**Precision milled** slots and **precision ground** serration, **burnished**.

**Material:**

Quality product made of 16MnCr5.

**Suitable for:**

**Heavy-duty chucks** from Schunk, Röhms and other heavy-duty chuck manufacturers.

**Optional extras:**

T-nuts No. 313505 – 313605.

**Note:**

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

|                       |        |
|-----------------------|--------|
| Hole centre spacing a | 24 mm  |
| for chuck type        | 210 mm |
| for thread DIN 912    | M12    |
| Height H              | 40 mm  |
| Bore spacing b        | 25 mm  |
| Slot width D          | 14 mm  |
| Length L              | 95 mm  |

|                          |                                   |
|--------------------------|-----------------------------------|
| Width B                  | 35 mm                             |
| suitable for colour code | Schunk heavy-duty chucks and jaws |
| Type of product          | Heavy-duty lathe chuck jaws       |