



ROTA-S-plus 2.0 self-centring three-jaw chuck with base and hard top jaws, DIN 702-4, Type: 250



Order data

Order number	313117 250
GTIN	2050001928771
Item class	33U

Description

Version:

- **Maximum concentricity and jaw exchange repeatability.**
- **Long service life with very high precision.**
- **Modular protective sleeve system.**
- **Very short set-up times.**
- **Chuck body case-hardened up to 315 mm Ø.**
- **Large aperture (dimension E!).**
- **Safety peg for maximum operator safety.**
- **Base jaws compatible with chucks of the system "F" and system "Duro".**
- **Flexible clamping of small and large components.**
- **High-precision clamping of very small internal Ø.**

Callout:

Hardened, extremely stiff and polished chuck body.

Base jaws with angled serrations.

Special shape with spray edge.

Push button for jaw change.

Jaw locking (3 times – apart from size 400).

Engagement pin for pre-positioning of the base jaw.

Actuation by means of a wrench

Application:

For machines with recessed mount or for mounting by means of flange. Secured with screws from the front. The flange blanks must always be fitted first to the machine and then matched to the chuck.

Standard:

DIN 702-4.

Material:

Entirely made of steel, suitable for high speeds (see table).

Supplied with:

1 safety chuck key and 1 set fastening screws.

1 set base jaws and hard top jaws.

Optional extras:

For spare and additional jaws see No. 313200 – 313350.

Technical description

Aperture E	62 mm
Clamping range with internal hard top jaws	92 - 252 mm
Clamping stroke per jaw S	7.7 mm
Weight	28.8 kg
Chuck key hexagon socket K	16 mm
maximum speed	4200 min ⁻¹
Chuck height D	98 mm
Type	250
Clamping range with external hard top jaws	10 - 250 mm
External Ø A	256 mm
Centring Ø B	235 mm
Series	ROTA-S plus
Standard	DIN 702-4
Colour code for accessories	Schunk self-centring chucks and jaws
Type of product	Self-centring chucks

Accessories

Hardened top jaw set, 3 pieces for chuck type 250	313250 250
Base jaw set, 3 pieces,angled serration for chuck type 250	313200 250
Base jaw set, 3 pieces,straight serration for chuck type 250	313207 250
Hardened top jaw set, 3 pieces for chuck type 250	313210 250
Base jaw set, 3 pieces,angled serration for chuck type 250	313205 250