

**Garant****ER clamping nut Internal, for ER: 40****Order data**

Order number	309621 40
GTIN	4062406093471
Item class	31Z

**Description****Version:**

Thread and taper ground in a single setup for highest concentricity.  
Internal clamping nut with an external thread. **With slots.**

**Suitable for:**

ER collet chucks with internal thread.

**Optional extras:**

Single open ended spanner (for size 16), No. 613300 size 25.  
Sealing rings No. 309625; 309630; 309635; 309645.

**Note:**

Collet chuck and clamping nut are balanced separately!

**Technical description**

Overall length L	20 mm
External $\varnothing$ D	50 mm
Thread	M50 $\times$ 1.5
for ER	40 mm

maximum tightening torque	120 Nm
Suitable C-hook (pin) spanner No. 628400	45/50
Standard	DIN 6499 D
Type of product	Clamping nut