

Garant**ER clamping nut Internal, for ER: 16****Order data**

Order number	309621 16
GTIN	4062406093440
Item class	31Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity.
Internal clamping nut with an external thread. **With hexagon 25 AF.**

Suitable for:

ER collet chucks with internal thread.

Optional extras:

Single open ended spanner (for size 16), No. 613300 size 25.

Sealing rings No. 309625; 309630; 309635; 309645.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

maximum tightening torque	40 Nm
for ER	16 mm
Thread	M24×1
External Ø D	24 mm

Overall length L	11 mm
Width across flats AF	19 mm
Standard	DIN 6499 D
Type of product	Clamping nut