



## Top jaws set, 3 pieces, for chuck type: 250



### Order data

Order number	313715 250
GTIN	2050001929709
Item class	33T

### Description

**Version:**

**Precision milled** slots and **precision ground** serration, **burnished**.

**Material:**

Quality product made of 16MnCr5.

**Suitable for:**

**Heavy-duty chucks** from Schunk, Röhms and other heavy-duty chuck manufacturers.

**Optional extras:**

T-nuts No. 313505 – 313605.

**Note:**

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

Length L	110 mm
Slot width D	16 mm
Height H	42 mm
for chuck type	250 mm
Bore spacing b	30 mm
for thread DIN 912	M12
Hole centre spacing a	30 mm

Width B	40 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws