



## Segment jaws set, 3 pieces, Aluminium, for chuck type: 210



### Order data

Order number	313437 210
GTIN	2050001929556
Item class	33T

### Description

**Version:**

**Precision milled** slots and **precision ground** serrations, **burnished**.

**Application:**

All-round low-distortion clamping.

**Material:**

Aluminium

**Suitable for:**

**Heavy-duty chucks** from Schunk, Röhmm and other heavy-duty chuck manufacturers.

**Optional extras:**

T-nuts No. 313505 – 313605.

**Note:**

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

for chuck type	210 mm
Length L	72.5 mm
Slot width D	17 mm
Width B	140 mm
Hole centre spacing a	35 mm
Bore spacing b	22 mm

Height H	58 mm
Type of product	Heavy-duty lathe chuck jaws