



ROTA-S 2.0 self-centring three-jaw chuck with short taper and base and hard top jaws, DIN 702-3, Type: 200/5



Order data

Order number	313137 200/5
GTIN	2050001928887
Item class	33U

Description

Version:

- **Maximum concentricity and jaw exchange repeatability.**
- **Long service life with very high precision.**
- **Modular protective sleeve system.**
- **Very short set-up times.**
- **Chuck body case-hardened up to 315 mm Ø.**
- **Large aperture (dimension E!).**
- **Safety peg for maximum operator safety.**
- **Base jaws compatible with chucks of the system "F" and system "Duro".**
- **Flexible clamping of small and large components.**
- **High-precision clamping of very small internal Ø.**

Application:

For spindle noses DIN 55027 with studs and collar nuts. The chuck is always fitted to the spindle nose directly without an intermediate flange.

Standard:

DIN 702-3.

Material:

Entirely made of steel, suitable for high speeds (see table).

Supplied with:

1 safety chuck key and 1 set fastening screws.

1 set base jaws and hard top jaws.

Optional extras:

For spare and additional jaws see No. 313200 – 313350.

Technical description

Type	200
Clamping stroke per jaw S	7 mm
Clamping range with external hard top jaws	8 - 208 mm
Aperture E	52 mm
Short taper arbor	5
maximum speed	4800 min ⁻¹
Weight	18.6 kg
External Ø A	206 mm
Clamping range with internal hard top jaws	72 - 224 mm
Size of studs	M10
Number of studs	4
Centring taper Ø B	82.575 mm
Chuck key hexagon socket K	12 mm
Series	ROTA-S plus
Standard	DIN 702-3
Colour code for accessories	Schunk self-centring chucks and jaws
Type of product	Self-centring chucks

Accessories

Hardened top jaw set, 3 pieces for chuck type 200	313250 200
Base jaw set, 3 pieces,angled serration for chuck type 200	313205 200
Base jaw set, 3 pieces,straight serration for chuck type 200	313207 200

Base jaw set, 3 pieces,angled serration for chuck type 200	313200 200
Hardened top jaw set, 3 pieces for chuck type 200	313210 200