

**Garant**
**Medium-Plus blade carrier for face grooving, right-hand, Ø range Groove D1 / D2: 54/75mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 274030 54/75  |
| GTIN         | 4062406093594 |
| Item class   | 21U           |

**Description**
**Version:**

For grooving inserts No. 275021 – 275048.  $D_2 = 999$  in the size designation corresponds to theoretically infinite.

**Application:**

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

**Attention:**

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

**Note:**

$D_1$  = minimum Ø for the first first groove /  $D_2$  = minimum Ø for the second groove.

**Technical description**

|                                 |            |
|---------------------------------|------------|
| maximum cutting depth $t_{max}$ | 26 mm      |
| maximum 1st groove Ø $D_2$      | 75 mm      |
| minimum 1st groove Ø $D_1$      | 54 mm      |
| Application type                | right-hand |
| System key                      | yes        |
| Groove width w                  | 3 mm       |

Type of product

Cartridges