

Sideboard with sliding doors, Width: 1200 mm



Order data

Order number	974210 1200
GTIN	2050002049635
Item class	91Q

Description

Version:

Sliding-door cabinet of wood with centre partition and 2 storage shelves (left and right of the centre partition) 25 mm thick, adjustable at 32 mm intervals. Cabinet with sturdy finished rear panel. Supplied with curved door handles. Steel base 30 mm high including levelling screws. Cylinder lock with 2 keys.

Colour:

of wood, with metal grey melamine coating. **Base metallic grey powder-coated.**

Height adjustment interval: 32 mm

Height: 779 mm

Width: 1200 mm

Depth: 450 mm

Usable height: 705 mm

Number of shelves: 2

Technical description

Width	1200 mm
compatible with integrated locking systems	no
Surface body	Wood
Number of shelves	2
Colour of handle	metallic grey

Usable height	705 mm
with base	yes
Grip shape	Curved handle
Electronic locking system can be retrofitted	no
Lock numbers individually interchangeable	no
Material of the base	Sheet metal
Depth	450 mm
Base height	30 mm
Height	779 mm
Colour of fronts	metallic grey
Colour of base	metallic grey
Colour of body	metal grey
Shelf thickness	25 mm
Height adjustment interval	32 mm
Type of product	Office cabinet