

Garant**Medium blade carrier for face grooving, right-hand, Ø range Groove D1 / D2: 27/40mm****Order data**

Order number	274020 27/40
GTIN	4062406093877
Item class	21U

Description**Version:**

For inserts No. 275000 – 275015.

Application:

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D_1 = minimum \varnothing for the first first groove / D_2 = minimum \varnothing for the second groove.

Technical description

maximum 1st groove $\varnothing D_2$	40 mm
maximum cutting depth t_{max}	24 mm
minimum 1st groove $\varnothing D_1$	27 mm
Application type	right-hand
System key	yes
Groove width w	4 mm

Type of product

Cartridges