

Garant**Medium blade carrier for face grooving, right-hand, Ø range Groove D1 / D2: 32/50mm****Order data**

| | |
|--------------|---------------|
| Order number | 274020 32/50 |
| GTIN | 4062406093884 |
| Item class | 21U |

Description**Version:**

For inserts No. 275000 – 275015.

Application:

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D_1 = minimum \varnothing for the first first groove / D_2 = minimum \varnothing for the second groove.

Technical description

| | |
|--------------------------------------|------------|
| maximum cutting depth t_{max} | 24 mm |
| minimum 1st groove $\varnothing D_1$ | 32 mm |
| maximum 1st groove $\varnothing D_2$ | 50 mm |
| Application type | right-hand |
| System key | yes |
| Groove width w | 4 mm |

Type of product

Cartridges