

**Garant**
**Heavy-Duty blade carrier for face grooving, right-hand, Ø range Groove D1 / D2: 144/200mm**

**Order data**

|              |                |
|--------------|----------------|
| Order number | 274070 144/200 |
| GTIN         | 4062406094065  |
| Item class   | 21U            |

**Description**
**Version:**

For grooving inserts No. 275021 – 275048.

**Application:**

In conjunction with toolholder No. 274004 or alternatively with adapter No. 274003 and suitable toolholder for parting-off tools.

**Attention:**

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

**Note:**

$D_1$  = minimum  $\varnothing$  for the first groove /  $D_2$  = maximum  $\varnothing$  for the first cut.

$D_2 = 999$  in the size designation corresponds to theoretically infinite.

**Technical description**

|                                      |            |
|--------------------------------------|------------|
| minimum 1st groove $\varnothing D_1$ | 144 mm     |
| maximum 1st groove $\varnothing D_2$ | 200 mm     |
| maximum cutting depth $t_{\max}$     | 70 mm      |
| Application type                     | right-hand |
| System key                           | yes        |
| Groove width $w$                     | 8 mm       |

Type of product

Cartridges