

Garant
Medium-Plus blade carrier for face grooving, left-hand, Ø range Groove D1 / D2: 69/100mm

Order data

Order number	274032 69/100
GTIN	4062406094164
Item class	21U

Description
Version:

For grooving inserts No. 275021 – 275048. $D_2 = 999$ in the size designation corresponds to theoretically infinite.

Application:

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D_1 = minimum \varnothing for the first first groove / D_2 = minimum \varnothing for the second groove.

Technical description

minimum 1st groove $\varnothing D_1$	69 mm
maximum cutting depth t_{max}	28 mm
maximum 1st groove $\varnothing D_2$	100 mm
Application type	left-hand
System key	yes
Groove width w	3 mm

Type of product

Cartridges