

**Garant**
**Medium-Plus blade carrier for face grooving, left-hand, Ø range Groove D1 / D2: 172/250mm**

**Order data**

Order number	274042 172/250
GTIN	4062406094294
Item class	21U

**Description**
**Version:**

For grooving inserts No. 275021 – 275048.  $D_2 = 999$  in the size designation corresponds to theoretically infinite.

**Application:**

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

**Attention:**

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

**Note:**

$D_1$  = minimum Ø for the first first groove /  $D_2$  = minimum Ø for the second groove.

**Technical description**

minimum 1st groove Ø $D_1$	172 mm
maximum cutting depth $t_{max}$	32 mm
maximum 1st groove Ø $D_2$	250 mm
Application type	left-hand
System key	yes
Groove width $w$	4 mm

Type of product

Cartridges