



Segment jaws set, 3 pieces, Aluminium, for chuck type: 250



Order data

Order number	313437 250
GTIN	2050001929563
Item class	33T

Description

Version:

Precision milled slots and **precision ground** serrations, **burnished**.

Application:

All-round low-distortion clamping.

Material:

Aluminium

Suitable for:

Heavy-duty chucks from Schunk, Röhm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

Height H	78 mm
for chuck type	250 mm
Bore spacing b	28 mm
Length L	87.5 mm
Width B	180 mm
Slot width D	21 mm

Hole centre spacing a	40 mm
Type of product	Heavy-duty lathe chuck jaws