

Garant
Heavy-Duty blade carrier for face grooving, left-hand, Ø range Groove D1 / D2: 114/160mm

Order data

| | |
|--------------|----------------|
| Order number | 274072 114/160 |
| GTIN | 4062406094416 |
| Item class | 21U |

Description
Version:

For grooving inserts No. 275021 – 275048.

Application:

In conjunction with toolholder No. 274004 or alternatively with adapter No. 274003 and suitable toolholder for parting-off tools.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D_1 = minimum \varnothing for the first groove / D_2 = maximum \varnothing for the first cut.

$D_2 = 999$ in the size designation corresponds to theoretically infinite.

Technical description

| | |
|--------------------------------------|-----------|
| minimum 1st groove $\varnothing D_1$ | 114 mm |
| maximum cutting depth t_{max} | 70 mm |
| maximum 1st groove $\varnothing D_2$ | 160 mm |
| Application type | left-hand |
| System key | yes |
| Groove width w | 8 mm |

Type of product

Cartridges