

Electrically height-adjustable office desk Beech, Width: 1600 mm



Order data

Order number	974020 1600
GTIN	
Item class	91Q

Description

Version:

Office desk with electric height adjustment using controls.
 Base bolted rectangular frame of 70×70 mm hollow section. The entire leg area of the frame is clear of obstructions, so mobile drawer units up to 620 mm in height can be accommodated under the desk. Speed travel when adjusting the height 50 mm /sec. Noise level less than 50 dB. Rail with flat profile, slightly curved, width 90 mm. Rail with pad for 15 mm height adjustment. Supplied with approach protection by means of resistance measurement.
 Melamine desk top with beech-effect surface.

Standard:

DIN EN 527-1/-2/-3 für Grundkonstruktion.

Colour:

Base frame metallic grey **powder-coated**.

Worktop thickness: 25 mm

Height adjustment range: 680 - 1180 mm

Width: 1600 mm

Depth: 800 mm

Worktop thickness: 25 mm

maximum load capacity: 75 kg

Weight: 65 kg

Technical description

Height adjustment range	680 - 1180 mm
Depth	800 mm

maximum load capacity	75 kg
Width	1600 mm
Worktop thickness	25 mm
Weight	65 kg
Type of height adjustment	electrical
Worktop thickness	25 mm