

## Office desk Light grey, Width: 2000 mm



### Order data

Order number	974041 2000
GTIN	2050002048263
Item class	91Q

### Description

#### Version:

Convenient office desk with stepless **height adjustment** (adjustment range **680 – 820 mm**).  
 Sturdy support frame with cross-bracing.  
 Leg sections of 2 mm steel square hollow section, 50/50 mm.  
 Connected with positive-fitting stiffening bracing.  
 Optimum legroom due to ergonomically designed frame.  
 Melamine table top 25 mm thick with **light grey surface**.

#### Colour:

Base frame metallic grey **powder-coated**.  
 Insert thickness: 25 mm  
 Height adjustment range: 680 - 820 mm  
 Width: 2000 mm  
 Depth: 800 mm  
 Worktop thickness: 25 mm

### Technical description

Worktop covering	Melamine
Depth	800 mm
Material of worktop	Laminated particle board coated with synthetic resin
Surface worktop	Plastic, light grey

Colour of worktop surface	light grey
Height adjustment range	680 - 820 mm
Width	2000 mm
Worktop thickness	25 mm
Insert shape	Rectangular
Height adjustment workstation	680-820 mm
Type of height adjustment	mechanical
Insert thickness	25 mm
Type of product	Office table

## Accessories

Cable pass-through Number of sleeves 2LR	974100 2LR
Cable pass-through Number of sleeves 1R	974100 1R
Cable pass-through Number of sleeves 1M	974100 1M
Cable pass-through Number of sleeves 1L	974100 1L
Folding cable duct suitable for table width 2000 mm	974120 2000
Under-desk modesty screen Metal suitable for table width 2000 mm	974111 2000
Under-desk modesty screen Wood suitable for table width 2000 mm	974110 2000
Acoustic partition wall Type 2000	974150 2000
PC-holder Type 1	974130 1