

Office desk Beech, Width: 1600 mm



Order data

Order number	974040 1600
GTIN	2050002048232
Item class	91Q

Description

Version:

Convenient office desk with stepless **height adjustment** (adjustment range **680 – 820 mm**).

Sturdy support frame with cross-bracing.

Leg sections of 2 mm steel square hollow section, 50/50 mm.

Connected with positive-fitting stiffening bracing.

Optimum legroom due to ergonomically designed frame.

Melamine table top 25 mm thick with **beech-effect surface**.

Colour:

Base frame metallic grey **powder-coated**.

Insert thickness: 25 mm

Height adjustment range: 680 - 820 mm

Width: 1600 mm

Depth: 800 mm

Worktop thickness: 25 mm

Technical description

Insert shape	Rectangular
Worktop thickness	25 mm
Height adjustment range	680 - 820 mm
Material of worktop	Laminated particle board coated with synthetic resin

Depth	800 mm
Worktop covering	Melamine
Surface worktop	Beech-effect finish
Width	1600 mm
Height adjustment workstation	680-820 mm
Type of height adjustment	mechanical
Insert thickness	25 mm
Type of product	Office table

Accessories

Cable pass-through Number of sleeves 2LR	974100 2LR
Cable pass-through Number of sleeves 1R	974100 1R
Cable pass-through Number of sleeves 1M	974100 1M
Cable pass-through Number of sleeves 1L	974100 1L
Folding cable duct suitable for table width 1600 mm	974120 1600
Under-desk modesty screen Metal suitable for table width 1600 mm	974111 1600
Under-desk modesty screen Wood suitable for table width 1600 mm	974110 1600
Acoustic partition wall Type 1600	974150 1600
PC-holder Type 1	974130 1