

Garant
Medium blade carrier for face grooving, right-hand, Ø range Groove D1 / D2: 24/35mm

Order data

Order number	274014 24/35
GTIN	4062406094478
Item class	21U

Description
Version:

For inserts No. 275000 – 275015.

Application:

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D_1 = minimum Ø for the first first groove / D_2 = minimum Ø for the second groove.

Technical description

maximum 1st groove Ø D_2	35 mm
maximum cutting depth t_{max}	12 mm
minimum 1st groove Ø D_1	24 mm
Application type	right-hand
System key	yes
Groove width w	3 mm

Type of product

Cartridges