



## Top jaws set, 3 pieces, for chuck type: 165



### Order data

Order number	313755 165
GTIN	2050001929778
Item class	33T

### Description

#### Version:

Bevelled for small clamping  $\emptyset$ .

**Precision milled** slots and **precision ground** serrations, **burnished**.

#### Material:

Quality product made of 16MnCr5.

#### Suitable for :

**Heavy-duty chucks** from Schunk, Röhmm and other heavy-duty chuck manufacturers.

#### Optional extras:

T-nuts No. 313505 – 313605.

#### Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

suitable for colour code: Schunk heavy-duty chucks and jaws

Length L: 82 mm

Width B: 32 mm

Height H: 32 mm

Hole centre spacing a: 15 mm

Bore spacing b: 20 mm

Slot width D: 12 mm

### Technical description

Height H	32 mm
Length L	82 mm

Bore spacing b	20 mm
for thread DIN 912	M10
for chuck type	165 mm
Slot width D	12 mm
Hole centre spacing a	15 mm
Width B	32 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws