

Garant**Medium blade carrier for face grooving, right-hand, Ø range Groove D1 / D2:
27/40mm****Order data**

Order number	274024 27/40
GTIN	4062406094690
Item class	21U

Description**Version:**

For inserts No. 275000 – 275015.

Application:

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D₁ = minimum Ø for the first first groove / D₂ = minimum Ø for the second groove.

Technical description

maximum cutting depth t _{max}	16 mm
minimum 1st groove Ø D ₁	27 mm
maximum 1st groove Ø D ₂	40 mm
Application type	right-hand
System key	yes
Groove width w	4 mm

Type of product

Cartridges