



## Push-out collet, round, to DIN 6343, 185 E, Clamping $\varnothing$ : 22mm



### Order data

Order number	329555 22
GTIN	4045197724786
Item class	34D

### Description

#### Version:

Collets, **round profile in 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

#### Standard:

**DIN 6343**

#### Accuracy:

**Concentricity tolerances:** D = 1 to 10 mm = 0.02 mm D = 10 to 30 mm = 0.03 mm D = 30 to 60 mm = 0.04 mm

#### Note:

Other diameters and profiles (e.g. square or hexagon) **on request!**

Profile  $\varnothing$  4.0 – 8.0 mm smooth. From  $\varnothing$  9.0 mm with transverse serrations.

### Technical description

Angle $\alpha$	15 degrees
K	84 mm
A	73 mm
Clamping $\varnothing$	22 mm
F	66 mm
Overall length L	110 mm
Type	185 E

Type of product

Collet