

Garant
Medium-Plus blade carrier for face grooving, right-hand, Ø range Groove D1 / D2: 120/180mm

Order data

Order number	274050 120/180
GTIN	4062406094812
Item class	21U

Description
Version:

For grooving inserts No. 275021 – 275048. $D_2 = 999$ in the size designation corresponds to theoretically infinite.

Application:

In conjunction with toolholder No. 274002 or alternatively with adapter No. 274001 and suitable toolholder for parting-off tools.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

Note:

D_1 = minimum Ø for the first first groove / D_2 = minimum Ø for the second groove.

Technical description

minimum 1st groove Ø D_1	120 mm
maximum cutting depth t_{max}	25 mm
maximum 1st groove Ø D_2	180 mm
Application type	right-hand
System key	yes
Groove width w	5 mm

Groove width w	6 mm
Type of product	Cartridges