

**FAHRION®**  
FAHRION® PRESSION
**Push-out collet, round, to DIN 6343, 185 E, Clamping Ø: 47mm**

**Order data**

Order number	329555 47
GTIN	4045197725035
Item class	34D

**Description**
**Version:**

Collets, **round profile in 1 mm increments. Please specify required clamping Ø with order.**

**Standard:**
**DIN 6343**
**Accuracy:**

**Concentricity tolerances:** D = 1 to 10 mm = 0.02 mm D = 10 to 30 mm = 0.03 mm D = 30 to 60 mm = 0.04 mm

**Note:**

Other diameters and profiles (e.g. square or hexagon) **on request!**

Profile Ø 4.0 – 8.0 mm smooth. From Ø 9.0 mm with transverse serrations.

**Technical description**

Angle $\alpha$	15 degrees
F	66 mm
A	73 mm
K	84 mm
Clamping Ø	47 mm
Overall length L	110 mm
Type	185 E

Type of product

Collet