

Garant
Medium-Plus blade carrier for face grooving, left-hand, Ø range Groove D1 / D2: 42/60mm

Order data

Order number	274046 42/60
GTIN	4062406095185
Item class	21U

Description
Version:

For grooving inserts No. 275021 – 275048. $D_2 = 999$ in the size designation corresponds to theoretically infinite.

Application:

In conjunction with toolholder No. 274002.

Attention:

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 1 separately.

Note:

D_1 = minimum Ø for the first groove / D_2 = maximum Ø for the first cut.

Technology values should be reduced by 30 – 50% depending on the clamping situation and material.

System key: yes

Groove width w : 4 mm

maximum cutting depth t_{max} : 18 mm

Technical description

maximum 1st groove Ø D_2	60 mm
minimum 1st groove Ø D_1	42 mm
maximum cutting depth t_{max}	18 mm

Application type	left-hand
System key	yes
Groove width w	4 mm
Type of product	Cartridges