

**Garant****Heavy-Duty blade carrier for face grooving, left-hand, Ø range Groove D1 / D2: 184/250mm****Order data**

|              |                |
|--------------|----------------|
| Order number | 274076 184/250 |
| GTIN         | 4062406095376  |
| Item class   | 21U            |

**Description****Version:**

For grooving inserts No. 275021 – 275048.

**Application:**

In conjunction with toolholder No. 274004 or alternatively with adapter No. 274003 and suitable toolholder for parting-off tools.

**Attention:**

Without clamping screws (these are supplied with the toolholders). Please order the assembly key No. 279940 separately.

**Note:**

$D_1$  = minimum  $\varnothing$  for the first groove /  $D_2$  = maximum  $\varnothing$  for the first cut.

$D_2 = 999$  in the size designation corresponds to theoretically infinite.

**Technical description**

|                                      |           |
|--------------------------------------|-----------|
| maximum cutting depth $t_{\max}$     | 50 mm     |
| maximum 1st groove $\varnothing D_2$ | 250 mm    |
| minimum 1st groove $\varnothing D_1$ | 184 mm    |
| Application type                     | left-hand |
| System key                           | yes       |
| Groove width $w$                     | 8 mm      |

Type of product

Cartridges