

**BENNING****Digital current clamp, Manufacturer's designation: CMP2****Order data**

Order number	473305 CMP2
GTIN	4014651446793
Item class	47A

**Description****Version:**

Robust and ergonomic plastic casing with illuminated LCD display. Reliable AC and DC measurements without breaking the operating circuit. Recording of measured value and maximum value, relative measurement.

**Application:**

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. Very high resolution of 10 mA AC in the 40 A measurement range. Integral Volt sensor (NCV) provides non-contact phase voltage signals and detects broken leads in cables (visual/acoustic). Inrush current measurement (INRUSH), low-pass filter (LPF), ZERO function.

**Standard:**

**IEC / EN 061010-1 (DIN VDE 0411-1).**

**Supplied with:**

Batteries, probe leads, compact protective case, operating instructions.

**Technical description**

AC current	10 mA – 400 A
maximum jaw aperture	23 mm

Basic accuracy	2 %
Measurement process	TRUE RMS
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Overvoltage category	CAT III 600 V
Memory function	HOLD
Information displayed	4200
DC current	10 mA – 400 A
Power supply	Battery-powered
Power supply	2× 081561 LR3
Calibration	I4
Type of product	Current clamp

## Services

CalibrationClamp meter Type D	027050 D
DAkkS calibrationClamp meter Type D	027060 D

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------