

**Garant****Tape measure, Band length: 5m****Order data**

Order number	462070 5
GTIN	4062406095628
Item class	41H

**Description****Version:**

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return. For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**. Plain bearings with Teflon ensure smooth action and exceptionally easy running. **Innovative dampers** of special rubber absorb the reaction energy and protect the wrist. **Aluminium profile** inserted on the underside for precise standing. A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

**Technical description**

Tape width	16 mm
Band length	5 m
Body height	69 mm
Body width	30 mm
Body length	70 mm
Standard	EG I

Calibration	G1
Type of product	Measuring tape

**Services**

CalibrationTape measure maximum length 5 m	026240 5
--	----------