



Pair of cold protection gloves 1603 W, Glove size: 9



Order data

Order number	094813 9
GTIN	4059904107281
Item class	09H

Description

Version:

1603 W. Seamless cold protection gloves with **latex coating**. The roughened coating offers a **very secure grip** when working with oily components. **Good visibility** due to neon yellow backing material.

Version of the advertising text:

1603 W. Seamless cold protection gloves with **latex coating**. The roughened coating offers a **very secure grip** when working with oily components. **Good visibility** due to neon yellow backing material.

Application:

For windy, cold or wet working conditions.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Cold protection	very good
Glove size	9
Material of coating	Latex
Heat protection	not available
Wet grip	very good
EN 388 tear propagation resistance	4
Oil grip	good
Accuracy of fit	good
Touch sensitivity	medium
EN 388 penetration resistance	1
EN 388 abrasion resistance	2
Breathability	good
silicone-free	no
DMF-free	no
EN 388 cut resistance	2
Protection category	Category II
Type of glove	Cold protection gloves
Contents	12
Application	reusable
Application range	All-round
Knitted technology	7G
Standard	EN 511
EN 388	2241X
EN 511	02X
Backing material	Cotton
Coating	Latex
Coating variant	The palms of the hands
Colour	blue / yellow

CE	CE 2241
Weight	45 g
Type of product	Cold protection gloves