

**Pair of gloves 6315, Glove size: 8****Order data**

Order number	094456 8
GTIN	4059904106987
Item class	09H

**Description****Version:**

6315. Cut-resistant gloves with good comfort for the wearer. Grey PU partial coating for good grip in dry and wet working conditions. Not suitable for dealing with oily components.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Touch sensitivity	very good
EN 388 tear propagation resistance	4
Accuracy of fit	good
Heat protection	not available
EN 388 penetration resistance	3
Oil grip	good

Material of coating	PU
DMF-free	no
Wet grip	medium
EN 388 cut resistance	3
EN 388 abrasion resistance	4
Glove size	8
silicone-free	no
Breathability	good
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	10
Knitted technology	13G
EN 388	4343C
Backing material	HPPE
Coating	PU
Coating variant	The palms of the hands
Application range	All-round
Colour	grey
Weight	15 g
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves