

Mitutoyo**Quick thickness gauge, Measuring range: 0-12mm**

Order data

Order number	438251 0-12
GTIN	4946368727332
Item class	44A

Description

Version:

Very small and handy device with a capacitive measuring system. Steel measuring faces hardened, ground and lapped.

Supplied with:

1 battery No. 081560 size 357.

Technical description

Number of batteries contained	1
Error limit	0.02 mm
Throat	20 mm
Article no of the battery / rechargeable battery fitted	081560 357
Scale divisions	0.01 mm
Measuring range	0 - 12 mm
Measuring face Ø	5 mm
Power supply	Battery-powered
Packaging	sturdy box
Standard	Manufacturer's standard

Measurement technology	digital
Calibration	C6
Type of product	Dial thickness gauges

Services

DAkkS calibrationDial thickness gauge maximum measuring range 30	023430 30
CalibrationDial thickness gauge maximum measuring range 200	023420 200

Accessories

Button cell / special battery Battery type 357	081560 357
--	------------