

**Mitutoyo****Quick thickness gauge, Measuring range: 0-12mm**

## Order data

|              |               |
|--------------|---------------|
| Order number | 438251 0-12   |
| GTIN         | 4946368727332 |
| Item class   | 44A           |

## Description

**Version:**

Very small and handy device with a capacitive measuring system. Steel measuring faces hardened, ground and lapped.

**Supplied with:**

1 battery No. 081560 size 357.

Calibration: C6

Packaging: sturdy box

Scale divisions: 0.01 mm

Error limit: 0.02 mm

Measuring face  $\varnothing$ : 5 mm

Throat: 20 mm

## Technical description

|   |            |
|---|------------|
| Number of batteries contained                           | 1          |
| Error limit   | 0.02 mm    |
| Throat  | 20 mm      |
| Article no of the battery / rechargeable battery fitted | 081560 357 |
| Scale divisions   | 0.01 mm    |
| Measuring range   | 0 - 12 mm  |

|                        |                         |
|------------------------|-------------------------|
| Measuring face Ø       | 5 mm                    |
| Power supply           | Battery-powered         |
| Packaging              | sturdy box              |
| Standard               | Manufacturer's standard |
| Measurement technology | digital                 |
| Packaging              | sturdy box              |
| Calibration            | C6                      |
| Type of product        | Dial thickness gauges   |

### Services

|   |            |
|---|------------|
| DAkkS calibration Dial thickness gauge                            | 011310     |
| Calibration Dial thickness gauge                                  | 013820     |
| Labelling laser-etched Type                                       | 018940     |
| DAkkS calibration Dial thickness gauge maximum measuring range 30 | 023430 30  |
| Calibration Dial thickness gauge maximum measuring range 200      | 023420 200 |

### Accessories

|  |            |
|--|------------|
| Button cell / special battery Battery type 357 | 081560 357 |
|--|------------|