



Pair of cold protection gloves 1603 W, Glove size: 10



Order data

Order number	094813 10
GTIN	4059904107304
Item class	09H

Description

Version:

1603 W. Seamless cold protection gloves with **latex coating**. The roughened coating offers a **very secure grip** when working with oily components. **Good visibility** due to neon yellow backing material.

Version of the advertising text:

1603 W. Seamless cold protection gloves with **latex coating**. The roughened coating offers a **very secure grip** when working with oily components. **Good visibility** due to neon yellow backing material.

Application:

For windy, cold or wet working conditions.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

EN 388 cut resistance	2
DMF-free	no
EN 388 abrasion resistance	2
EN 388 penetration resistance	1
Touch sensitivity	medium
silicone-free	no
Heat protection	not available
Material of coating	Latex
Wet grip	very good
Accuracy of fit	good
Breathability	good
Cold protection	very good
Oil grip	good
EN 388 tear propagation resistance	4
Glove size	10
Protection category	Category II
Type of glove	Cold protection gloves
Contents	12
Application	reusable
Application range	All-round
Knitted technology	7G
Standard	EN 511
EN 388	2241X
EN 511	02X
Backing material	Cotton
Coating	Latex
Coating variant	The palms of the hands
Colour	blue / yellow

CE	CE 2241
Weight	45 g
Type of product	Cold protection gloves