

Ansell
Pair of gloves HyFlex® 11-423, Glove size: 7

Order data

Order number	094471 7
GTIN	10076490053434
Item class	04P

Description
Version:

HyFlex® 11-423. Water-based PU-nitrile coating. Free of silicone and DMF. Heat-resistant up to 100 °C. Particularly suitable for cutting to length of dry or oil-wetted parts.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Accuracy of fit	very good
Breathability	good
DMF-free	yes
Wet grip	good
Oil grip	good
EN 388 cut resistance	3

silicone-free	yes
EN 388 penetration resistance	2
EN 388 tear propagation resistance	3
Heat protection	not available
Material of coating	PU/nitrile
Touch sensitivity	good
EN 388 abrasion resistance	4
Glove size	7
Series	HyFlex®
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	DMF-free
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Foodstuffs certified
Knitted technology	13G
EN 388	4X32B
EN 407	X1XXXX
Backing material	INTERCEPT™
Coating	PU/nitrile
Material	PU/nitrile
Coating variant	The palms of the hands
Application range	All-round
Colour	grey / lime
Standard	EN 407
Weight	30 g
Length	225 mm
Application	reusable

Cut protection class	B
Type of product	Cut-resistant gloves