



## Pair of cold protection gloves 1603 W, Glove size: 8



### Order data

Order number	094813 8
GTIN	4260144428481
Item class	09H

### Description

**Version:**

**1603 W.** Seamless cold protection gloves with **latex coating**. The roughened coating offers a **very secure grip** when working with oily components. **Good visibility** due to neon yellow backing material.

**Version of the advertising text:**

**1603 W.** Seamless cold protection gloves with **latex coating**. The roughened coating offers a **very secure grip** when working with oily components. **Good visibility** due to neon yellow backing material.

**Application:**

For windy, cold or wet working conditions.

**Use of the advertising text:**

For windy, cold or wet working conditions.

**Standard:**

EN 388; EN 511

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Note re advertising text:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

## Technical description

EN 388 penetration resistance	1
Heat protection	not available
Breathability	good
Wet grip	very good
EN 388 cut resistance	2
Touch sensitivity	medium
Accuracy of fit	good
EN 388 abrasion resistance	2
Oil grip	good
DMF-free	no
Glove size	8
Cold protection	very good
silicone-free	no
EN 388 tear propagation resistance	4
Material of coating	Latex
Protection category	Category II
Type of glove	Cold protection gloves
Contents	12
Application	reusable
Application range	All-round
Knitted technology	7G
Standard	EN 511
EN 388	2241X
EN 511	02X
Backing material	Cotton
Coating	Latex
Coating variant	The palms of the hands
Colour	blue / yellow

CE	CE 2241
Weight	45 g
Type of product	Cold protection gloves