

BENNING**Digital current clamp, Manufacturer's designation: CM1-2****Order data**

Order number	473305 CM1-2
GTIN	4014650440624
Item class	47A

Description**Version:**

Robust and ergonomic plastic casing with illuminated LCD display. Reliable AC and DC measurements without breaking the operating circuit. Recording of measured value and maximum value, relative measurement.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions.

Standard:

IEC / EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions.

Technical description

AC current	0.1 A – 400 A
Basic accuracy	1 %
maximum jaw aperture	30 mm
DC voltage	0.1 V – 600 V

Resistance	0.1 Ω – 20 M Ω
Overvoltage category	CAT III 600 V
AC voltage	0.1 V – 600 V
Measurement process	RMS
Memory function	5
Manufacturer's designation	CM1-2
acoustic continuity test	0 – 20 Ω
Information displayed	2000
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	2
Power supply	Battery-powered
Power supply	2× 081561 LR3
Calibration	I4
Type of product	Current clamp

Services

DAkkS calibrationClamp meter Type D	027060 D
CalibrationClamp meter Type D	027050 D

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
Test leads Measuring tips \varnothing 4 mm	473308 4
Test leads Measuring tips \varnothing 2 mm	473308 2