

BENNING**Digital current clamp, Manufacturer's designation: CM2****Order data**

Order number	473305 CM2
GTIN	4014651000810
Item class	47A

Description**Version:**

Robust and ergonomic plastic casing with illuminated LCD display. Reliable AC and DC measurements without breaking the operating circuit. Recording of measured value and maximum value, relative measurement.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. Ideal for measuring small currents.

Standard:

IEC / EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions.

Calibration: I4

Information displayed: 4000

Basic accuracy: 0.5 %

acoustic continuity test: 0 – 50 Ω

Measurement process: TRUE RMS (AC)

Memory function: HOLD, MAX

AC voltage: 1 mV – 600 V

Technical description

Information displayed	4000
Resistance	0.1 Ω – 40 M Ω
Memory function	HOLD, MAX
maximum jaw aperture	25 mm
Manufacturer's designation	CM2
AC current	100 mA – 300 A
acoustic continuity test	0 – 50 Ω
Measurement process	TRUE RMS (AC)
DC voltage	0.1 mV – 600 V
Overvoltage category	CAT III 300 V
AC voltage	1 mV – 600 V
DC current	10 mA – 300 A
Basic accuracy	0.5 %
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	2
Power supply	Battery-powered
Power supply	2x 081561 LR3
Calibration	I4
Type of product	Current clamp

Services

Calibration Current clamp Type D	017720 D
Labelling laser-etched Type	018940
DAkkS calibration Current clamp Type D	016790 D
DAkkS calibration Clamp meter Type D	027060 D
Calibration Clamp meter Type D	027050 D

Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Test leads Measuring tips Ø 2 mm	473308 2
Test leads Measuring tips Ø 4 mm	473308 4