

KERN**Pocket scales, type TGC, maximum weighing range: 1000g**

Order data

Order number	479446 1000
GTIN	4045761214255
Item class	47D

Description

Version:

- **With cumulative weighing function, tare button.**
- **Calibration programme CAL for high accuracy.**

Flat pocket scales with large stainless steel weighing platform and handy tare dish. Backlit LCD display for easy reading of the weighed value.

Supplied with:

Supplied with 2 batteries No. 081560 size CR2032.

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
maximum weighing range	1000 g
Width	100 mm
Depth	130 mm
Number of batteries contained	2
Height	18 mm
Scale divisions	1 g

Net weight	0.18 kg
Power supply	Battery-powered
Calibration	K2
Type of product	Compact balance

Services

DAkkS calibration Scales maximum weighing range 50	027710 50
Calibration Scales maximum weighing range 50 kg	027700 50

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------