

KERN**Platform scales, type EOC, maximum weighing range: 35kg**

Order data

Order number	479606 35
GTIN	4045761192409
Item class	47D

Description

Version:

- **Robust stainless steel platform scales can be used as parcel, industrial, and counting scales.**
- **Dual-range scales with automatic changeover between the ranges (more precise display in the lower half of the weighing range).**
- **Display unit with numeral height 24 mm can be remote from platform; can be stood or mounted using flexible cable.**
- **High mobility due to optional battery operation and compact design.**
- **Provides an optical and acoustic signal to support portioning, metering or sorting within the tolerance range.**
- **Percentage determination: Enable weighing out to a prescribed value (100%) and determination of deviations from that set value.**
- **Quantity counting: Easy counting function allows quick counting of large numbers. Reference quantities selectable 5, 10, 25, 50 pieces.**
- **CAL calibration programme: For setting the accuracy (external calibration weight required for this available on request).**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with mains adapter, table base including wall bracket, protective hood.

Technical description

Reproducibility	10 g
Settling time	2 s
Net weight	5.2 kg
Manufacturer's designation	Type EOC
maximum weighing range	0 - 35 kg
Minimum unit weight	10 g
Scale divisions	5 g
Dimensions of weighing plate	300×300 mm
Calibration	K2
Reading at top of weighing range	10 g
IP Index of Protection	IP 65
Power supply	Mains operated
Interface	RS232C interface
Type of product	Platform balance

Services

CalibrationScales maximum weighing range 50 kg	027700 50
DAkkS calibrationScales maximum weighing range 50	027710 50