

**KERN****Platform scales, type EOC, maximum weighing range: 60Lkg**

## Order data

Order number	479606 60L
GTIN	4045761192300
Item class	47D

## Description

### Version:

- **Robust stainless steel platform scales can be used as parcel, industrial, and counting scales.**
- **Dual-range scales with automatic changeover between the ranges (more precise display in the lower half of the weighing range).**
- **Display unit with numeral height 24 mm can be remote from platform; can be stood or mounted using flexible cable.**
- **High mobility due to optional battery operation and compact design.**
- **Provides an optical and acoustic signal to support portioning, metering or sorting within the tolerance range.**
- **Percentage determination: Enable weighing out to a prescribed value (100%) and determination of deviations from that set value.**
- **Quantity counting: Easy counting function allows quick counting of large numbers. Reference quantities selectable 5, 10, 25, 50 pieces.**
- **CAL calibration programme: For setting the accuracy (external calibration weight required for this available on request).**

### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

### Supplied with:

Supplied with mains adapter, table base including wall bracket, protective hood.

## Technical description

Settling time	2 s
Minimum unit weight	20 g
Manufacturer's designation	Type EOC
Reading at top of weighing range	20 g
Calibration	K2
Scale divisions	10 g
maximum weighing range	0 - 60 kg
Dimensions of weighing plate	500×400 mm
Reproducibility	20 g
Net weight	9 kg
IP Index of Protection	IP 65
Power supply	Mains operated
Interface	RS232C interface
Type of product	Platform balance

## Services

CalibrationScales maximum weighing range 100 kg	027700 100
DAkkS calibrationScales maximum weighing range 180	027710 180