

BENNING
Digital current clamp, Manufacturer's designation: CM5-1
Order data

Order number	473305 CM5-1
GTIN	4014651440661
Item class	47A

Description
Version:

Sturdy plastic casing with large-format, 4 inch and 3 1/2 inch LCD display.
Reliable AC and DC measurements without breaking the operating circuit. Collection of measured value and maximum value, relative measurement.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. Automatic selection of the correct measurement function, measurement errors eliminated, quick response time and low input impedance (LoZ).

Standard:

IEC / EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions.

Calibration: I4

Information displayed: 9999

Basic accuracy: 0.9 %

acoustic continuity test: 0 – 30 Ω

Measurement process: TRUE RMS (AC)

Memory function: 5

AC voltage: 1.3 V – 750 V

Technical description

Norm	
Material of the housing	
Calibration	I4
Interface	
Type of product	Current clamp

