

BENNING**Digital current clamp, Manufacturer's designation: CM7****Order data**

Order number	473305 CM7
GTIN	4014651440593
Item class	47A

Description**Version:**

Robust and ergonomic plastic casing with illuminated LCD display. Reliable AC and DC measurements without breaking the operating circuit. Recording of measured value and maximum value, relative measurement.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions.

Standard:

IEC / EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions.

Calibration: I4

Information displayed: 4000

Basic accuracy: 0.7 %

acoustic continuity test: 0 – 30 Ω

Measurement process: TRUE RMS (AC)

Memory function: HOLD, MAX / MIN

AC voltage: 0.1 V – 750 V

Technical description

Measurement process	TRUE RMS (AC)
Manufacturer's designation	CM7
DC voltage	0.1 V – 1000 V
acoustic continuity test	0 – 30 Ω
DC current	0.1 A – 1000 A
maximum jaw aperture	53 mm
AC current	0.1 A – 1000 A
Resistance	0.1 Ω – 400 Ω
Overvoltage category	CAT IV 600 V
Frequency	1 Hz – 400 Hz
AC voltage	0.1 V – 750 V
Memory function	HOLD, MAX / MIN
Basic accuracy	0.7 %
Information displayed	4000
Article no of the battery / rechargeable battery fitted	081561 6LR61
Number of batteries contained	1
Power supply	Battery-powered
Power supply	1× 081561 6LR61
Calibration	I4
Type of product	Current clamp

Services

Labelling laser-etched Type	018940
Calibration Current clamp Type D	017720 D
DAkkS calibration Current clamp Type D	016790 D
Calibration Clamp meter Type D	027050 D
DAkkS calibration Clamp meter Type D	027060 D

Accessories

Alkaline-manganese batteries International size 6LR61	081556 6LR61
Alkaline-manganese batteries International size 6LR61	081561 6LR61