



Slim electrician's screwdriver for PlusMinus screws, Classic fully insulated, Profile size: 1



Order data

Order number	668392 1
GTIN	7610733278435
Item class	63E

Description

Version:

Handle and blade **fully insulated up to 1000 V to DIN EN 60900 / VDE 0682-201**. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Slim handle with a non-allergenic elastomer coating and a core of particularly tough and impact-resistant polypropylene. Due to its special surface structure, the grip is non-slip even with oily or wet hands.

Blade of PB Swiss Tools special alloy combines maximum hardness with exceptional toughness.

Reduced blade Ø with integral protective insulation for deep-lying screws and spring elements (blade Ø = insulation Ø near the tip of the blade).

Application:

For use at voltages up to 1000 V.

The screwdriver drive tip fits perfectly into the **PlusMinus screws (combination Pozidriv / slot-head)**, which are primarily used in electrical installation components.

Technical description

Profile Pozidriv – slot head	1 – 0.7×4.5
overall length	175 mm
Profile size	1
Blade length	80 mm
Series	Classic VDE
Standard	DIN EN IEC 60900 / VDE 0682-201

Drive profile	Combination profile screwdriver Pozidriv/slot-head
Type of product	Screwdrivers