

Garant**Pull-out shelf for rack, Usable depth 1350 mm, Extended shelf length: 100%****Order data**

Order number	993101 100
GTIN	4062406097493
Item class	91W

Description**Version:**

Pull-out storage shelf **with raised edge on 3 sides** (35 mm high) and practical **slide handle**. Insertion slots at 50 mm intervals. The pull-out shelf can also be installed behind a pair of swing doors. The pull-out shelf engages in the locking bar – thus activating the **anti-tilt lock**. The pin engages in the frame stiles, thus activating the **lateral locking** also. This locking engages when pushed in. Release the lock by pulling a handle under the push handle (single-hand operation). When fully extended the pull-out shelf locks in the frame stiles (double locking). Can be lifted by crane even when extended, since the pull-out shelf is locked. **Load capacity 1000 kg** evenly distributed. Pull-out shelves are supplied with safe working load labels.

Colour:

Anthracite RAL 7016 **powder-coated**.

Note:

Beech ply shelf No. 993170 can be inserted into the pull-out shelf.

Technical description

Pull-out shelf load capacity	1000 kg
Pull-out shelf installation height	300 mm
Extended shelf length	100 %
Application range	Heavy-duty racking

Material thickness	1.5 mm
Drawer/pull-out shelf load capacity	1000 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Usable depth 1350 mm
Height	300 mm
Width	920 mm
Depth	1300 mm
Usable height	35 mm
Usable width	830 mm
Usable depth	1200 mm
for rack bay usable width	920 mm
Type of product	Pull-out shelf