



## Pair of gloves HyFlex® 11-423, Glove size: 10



### Order data

Order number	094471 10
GTIN	10076490053465
Item class	04P

### Description

#### Version:

HyFlex® 11-423. Water-based PU-nitrile coating. Free of silicone and DMF. Heat-resistant up to 100 °C. Particularly suitable for cutting to length of dry or oil-wetted parts.

#### Standard:

EN 388; EN ISO 21420

#### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

### Technical description

Wet grip	good
Breathability	good
Heat protection	not available
Material of coating	PU/nitrile
EN 388 penetration resistance	2
silicone-free	yes

EN 388 abrasion resistance	4
EN 388 tear propagation resistance	3
Touch sensitivity	good
EN 388 cut resistance	3
DMF-free	yes
Glove size	10
Accuracy of fit	very good
Oil grip	good
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	DMF-free
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Foodstuffs certified
Knitted technology	13G
EN 388	4X32B
EN 407	X1XXXX
Backing material	INTERCEPT™
Coating	PU/nitrile
Material	PU/nitrile
Coating variant	The palms of the hands
Application range	All-round
Colour	grey / lime
Standard	EN 407
Weight	30 g
Length	225 mm
Application	reusable

Cut protection class	B
Type of product	Cut-resistant gloves