

Workshop accessories assortment, Number of tools: 9



Order data

Order number	954986 9
GTIN	2050002005112
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 954986: 1 pc.

GARANT LED torch No. 081505 size 125: 1 pc.

Claw retriever No. 081610 size 500: 1 pc.

HOLEX telescopic inspection mirror No. 081630 size 30: 1 pc.

EDDING permanent marker No. 085130 size R: 1 pc.

UVEX safety goggles No. 096515 size CLEAR: 1 pc.

HOLEX tweezers, rounded tips, No. 727550 size AM: 1 pc.

Snap-off blades, No. 845010 size 10: 1 pc.

GARANT universal trimming knife No. 845020: 1 pc.

Telescopic inspection lamp No. 081665: 1 pc.

Degree of fill of a drawer in units: 10x24

Width: 250 mm

Depth: 600 mm

Width in G: 10

Depth in G: 24

Technical description

Width	250 mm
-------	--------

Number of tools	9
Depth	600 mm
Depth in G	24
Width in G	10
Version	with tool kit
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×24
Type of product	Rigid foam inlay

Accessories

Tweezers, rounded tips 3 mm wide, 145 mm, form 40 Material AM	727550 AM
LED torcheswith batteries Type 125 mm	081505 125
Permanent marker Writing colour R	085130 R
Telescopic inspection lamp	081665
Comfort safety glassesuvex i-vo Lens tinting CLEAR	096515 CLEAR
LED torcheswith batteries Type 130 mm	081505 130
Snap-off "experience" blades set, 10 pieces, 18 mm number 10	845010 10
General-purpose knife with 2-component handlewith 3 blades, 18 mm	845020
Rigid foam inlay for tool sets suitable for rigid foam set 954986	952001 954986
Telescopic inspection mirror Mirror dimensions 30 mm	081630 30
Claw retriever Length 500 mm	081610 500